



Specifications:

- Primary voltage: 115VAC 60Hz
- Primary exciting current: 65mA (max.)
- Secondary voltage (full load): 12.6CTV .3Amp \pm 5%
- Breakdown voltage (Hi-pot):
1500VAC @ 60Hz for 1 minute between Primary to Secondary & core
500VAC @60Hz for 1 minute between Secondary to Secondary & core
- Insulation test: 100M Ω @ 500VDC
- Strain relief test: leads shall withstand a pull of 2.5kgs for 15 sec.
- Terminal length: 150 mm \pm 10mm
- Strip and tin: 10mm \pm 2mm
- UL 1015 and UL 1007 22AWG

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Xicon:](#)

[41LG300](#)