

Part Number . . .

ABF.00.250.CTA

Size/Series 00 / 00

[Request a quote](#)

MECHANICAL DETAILS




Shell Style/Model ABF*: Adapter from LEMO plug to BNC receptacle

Keying Circular (can rotate)

Housing Material Brass (chrome plated) shell and collet nut, nickel plated brass latch sleeve and mid pieces

Cable Fixing Variant : 0 - 0 mm

	A	L	M	Weight
mm.	11.5	36	28	8.3
in.	0.45	1.42	1.10	0.33

[Copyright](#) [Privacy policy](#) [Product safety](#)

PERFORMANCE DETAILS

Insert Configuration 0.25 : 1 Coax (50 Ohm)

Insulator T: PTFE

Specifications

Contact Type: Coaxial 50 Ohm

Max. Matings: 500

Contact Dia.: 0.7 mm (0.03in)

OTHER CHARACTERISTICS

Endurance (Shell) 3839 mating cycles

F ret (min): 100 N

IP Rating 50

Catalog



