




THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO CW INDUSTRIES INCORPORATED AND ITS AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN CW INDUSTRIES PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM CW INDUSTRIES INCORPORATED, SOUTHAMPTON, PENNSYLVANIA USA.

Rating	16A 125VAC, 10A 277VAC 3/4HP 125/277VAC			Mounting Hole 	Circuit Diagram 												
	21A 14V DC																
Contact Resistance		50m ohm max.		<table><tr><th>Thickness</th><th>X</th><th>Y</th></tr><tr><td>0.75 - 1.25</td><td>21.2 ± 0.1</td><td>36.6 ± 0.1</td></tr><tr><td>1.25 - 2.00</td><td>21.2 ± 0.1</td><td>36.8 ± 0.1</td></tr><tr><td>2.00 - 3.00</td><td>21.2 ± 0.1</td><td>37.0 ± 0.1</td></tr></table>	Thickness	X	Y	0.75 - 1.25	21.2 ± 0.1	36.6 ± 0.1	1.25 - 2.00	21.2 ± 0.1	36.8 ± 0.1	2.00 - 3.00	21.2 ± 0.1	37.0 ± 0.1	SPDT ON - ON
Thickness	X	Y															
0.75 - 1.25	21.2 ± 0.1	36.6 ± 0.1															
1.25 - 2.00	21.2 ± 0.1	36.8 ± 0.1															
2.00 - 3.00	21.2 ± 0.1	37.0 ± 0.1															
Insulation Resistance		DC 500V 100M ohm min.															
Dielectric Strength		AC 1500V 1 minute															
Operating Temperature		-20 °C ~ 85 °C															

BASE COLOR: Black
BUTTON COLOR: Black



RoHS Compliant

1 | Added 3/4HP 125/277VAC to rating. 1/31/11.

 INDUSTRIES Southampton, Pa. 18966 Tel 215.355.7080/www.cwind.com	Date Drawn: 1/31/11	Rev. 1	Unit: mm	Checked By: G.GULD
	Title: ROCKER SWITCH	CW P/N: GRB263C001NNN		