

# HUBER+SUHNER® DATA SHEET

## Coaxial Cable Connector: 16\_N-50-12-9/033\_-

Rev.: E



### Description

Right angle cable plug

QUICK-FIT connector

For outdoor applications

Water protection according to IP 68

### Technical Data

#### Electrical Data

Impedance	50 Ω
Interface frequency max.	11 GHz
Frequency range	DC to 2.5 GHz
Return loss	≥ 30 dB
Intermodulation	≤ -155 dBc (2 x 43 dBm carrier)

#### Mechanical Data

Centre contact	plugged
Outer contact	clamped
Weight	0.1891 kg

#### Environmental Data

Operating Temperature	-65 °C to 165 °C
2002/95/EC (RoHS)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Silver Plating
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE / PPO	SUCOPLATE (R) Plating
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	MVQ (Silicone Rubber)	

#### Related Documents

Outline drawing	DOU-00007094
Catalogue drawing	DOU-00007096
Assembly instruction	DOC-0000179113

#### Ordering Information

Single package	16_N-50-12-9/033_-E
----------------	---------------------

#### Additional Information

Suitable cables	SUCOFEED_1/2, SUCOFEED_1/2_FR, SUCOFEED_1/2_FR_UL, SUCOFEED_1/2_LW, Heliax LDF4-50A, NK Cables RF 1/2-50, Cellflex LCF12-50
Interface standards	IEC 61169-16_MIL-STD-348A/304_CECC 22210

HUBER+SUHNER is certified according to ISO 9001 and ISO 14001

#### WAIVER!

It is exclusively in written agreements that we provide our customers with warrants and representations as to the technical contained specifications and/or the fitness for any particular purpose. The facts and figures herein are carefully compiled to the best of our knowledge, but they are intended for general informational purposes only.



HUBER+SUHNER AG

RF Technology

9100 Herisau, Switzerland

Phone +41 (0)71 353 41 11

Fax +41 (0)71 353 45 90

[www.hubersuhner.com](http://www.hubersuhner.com)

**HUBER+SUHNER – Excellence in Connectivity Solutions**