

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0887388200

Status:

Active

Overview:

USB

Description:

Universal Serial Bus (USB) Shielded I/O Cable Assembly: A-to-Pigtail Sub-Channel, 2.08m (6.82') Length

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

General

Product Family

Cable Assemblies

Series

88740

Comments

Sub-Channel

Connector to Connector

USB Type A-to-Pigtail

Overview

USB

Product Name

USB

Physical

Cable Length

2.08m (6.82')

Circuits (Loaded)

4

Gender

Male

Lock to Mating Part

Yes

Packaging Type

Bag

Pitch - Mating Interface (in)

0.079 In, 0.098 In

Pitch - Mating Interface (mm)

2.00 mm, 2.50 mm

Single Ended

Yes

Wire Insulation Diameter

N/A

Wire Size AWG

N/A

Wire/Cable Type

N/A

Electrical

Current - Maximum

1A

Shielded

Yes

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-88738-001



image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

88740Series

Mates With

Universal Serial Bus (USB) Type A Receptacle [67329](#) , [67230](#) , [89485](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION