

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

09-01-6151

Status:

Active

Overview:

Edge Card Connectors

Description:

3.96mm Pitch KK® Crimp Housing, Edge Card Connector, Single-Sided, Surface Mount, Polarized, without Flange, 15 Circuits, Rib between 4 & 5, 7 & 8, 11 & 12

Documents:

3D Model

Packaging Specification PK-2574-001 (PDF)

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Edge Card Connectors

Series

2574

Component Type

Edgecard to Wire

Overview

Edge Card Connectors

Product Name

Edge Card, KK®

UPC

800753844810

Physical

(p)ower-(s)ignal Configuration

15s - 0p

Circuits (Loaded)

15

Circuits (maximum)

15

Color - Resin

Natural

Durability (mating cycles max)

25

Entry Angle

Vertical (Top Entry)

Flammability

94V-2

Keying to Mating Part

Yes

Material - Plating Mating

N/A

Material - Resin

Nylon

Net Weight

4.757/g

PCB Retention

None

PCB Thickness - Recommended

1.60mm

Packaging Type

Bag

Panel Mount

Without Flange

Pitch - Mating Interface

3.96mm

Polarized to Mating Part

Yes

Temperature Range - Operating

0°C to +75°C

Termination Interface: Style

N/A

Electrical

Current - Maximum per Contact

4.25A, 4.5A, 4.75A, 4A, 5A

Voltage - Maximum

250V

Material Info

Old Part Number

2574-15A9

Reference - Drawing Numbers

Packaging Specification

PK-2574-001

Sales Drawing

SD-2574




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2574Series

Mates With

PCB, 1.60mm Max. Thickness

Use With

2878 Terminals, 2478 Terminals, 2578 Terminals, Bifurcated