

SHF-110-01-L-D-RA

ESHF-125-01-L-D-SM-LC

EHF-108-01-F-D-SM-LC

ESHF-105-01-L-D-SM

EHF-125-01-L-D-SM-LC

(1.27 mm) .050"

SHF, ESHF, EHF, ECF SERIES

SHROUDED & EJECTOR IDC HEADER

SHF, ESHF Mates with:

FFSD, FFTP (SHF)

EHF Mates with:

FFSD*, FFTP

SPECIFICATIONS

For complete specifications see www.samtec.com?SHF, www.samtec.com?ESHF or www.samtec.com?EHF

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Sn or Au over

50 μ " (1.27 μ m) Ni

Operating Temp Range:

-55 °C to +125 °C

RoHS Compliant:

Yes

PROCESSING

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0.10 mm) .004" max

RECOGNITIONS

For complete scope of recognitions see www.samtec.com/quality




FILE NO. E111594

ALSO AVAILABLE (MOQ Required)

- Other sizes

EJECTOR HEADER CAP (Locks FFSD cable to EHF header)





ECF

NO. PINS PER ROW

05, 08, 10,
13, 17, 20, 25

***Important Note:**
EHF will not mate to FFSD with strain relief (-SR option), see ESHF series.

Note: Some lengths, styles and options are non-standard, non-returnable.



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.