



www.hellermanntyton.co.uk | [Products](#) | [Cable Ties and Fixings](#) | [Fixing Ties](#)

1-Piece Fixing Ties for Weld Studs T50SOSSBD-M8



T50SOSSBD for cable routing alongside and below the stud, Article number: 157-00039

- One-piece fixing ties
- High specification materials
- Superior design
- Suitable for complex applications

Primarily designed for use in the automotive industry, these parts can be used in a wide variety of applications where 5mm/8mm weld studs or 5mm/8mm ISO bolts are used and cables need to be bundled and secured. (WS series, T120RSM, DCT9 & DCT 11 are for 1/4" bolts)



Base Data

Colour	Black (BK)
Fixation Method (FF)	Weld Stud Fixing
Identification Plate Position	none
Mounting Screw Type	M8
Product Family	T50SOSSBD for cable routing alongside and below the stud
Product Group	1-Piece Fixing Ties for Weld Studs
Releasable Closure (Yes/No)	No
Tie Closure	plastic pawl
Type	T50SOSSBD-M8-HSW
Variant	Outside Serrated

Product Dimensions

Bundle Ø max.	30.0 mm
Bundle Ø max. (imperial)	1.2 "
Bundle Ø min.	3.0 mm
Bundle Ø min. (imperial)	0.12 "
Height (H2) (imperial)	0.6 "
Length (L)	175 mm
Length (L) (imperial)	7 "
Min. Tensile Strength (lbs)	50 lbs
Min. Tensile Strength (N)	150 N
Stud Ø	8.0 mm
Thickness (T)	1.3 mm
Width (W)	5.7 mm
Width (W) (imperial)	0.22 "

Logistic and Packaging

Carton Quantity	3000 pcs.
EAN code	4944387950885
Pack Cont.	100
Quantity per	Bag
UPC	089306298601
Weight (Kg)	0.3 kg

Material and Specifications

Flammability	UL94 V2
Material	PA66HSW
Material	Polyamide 6.6 heat and UV stabilised (PA66HSUV)

Operating Temperature -40 °C to +110 °C

More Information

UNSPSC Key 39121717

© HellermannTyton 2013