





Disconnect Terminals

Disconnect Terminals			SAKR		SAKR-D With StB test points		SAKC 4		SAKC 10		
											
			Lever		Plug		Pull Pin		Pull Pin		
Terminal Block Selection Data											
Available Options			Version								
With 2 StB test points KrS PA			0412260000	0183360000	0546460000*						
With 2 StB test points KrS Blue PA			0412280000	0183380000							
With 2 StB test points KrS without diode PA					0413160000*						
Beige PA			0412160000	0172160000	0412960000* 0299960000*						
Blue PA			0412180000	0172180000							
Without diode PA					0413060000** 0185760000**						
With diode PA					0263360000*** 0299560000***						
Orange PA			1461960000								
KrG			0412120000				0340720000	0357520000	0324020000		
KrS									0324030000		
With 1 StB test point KrG									1404520000		
With 2 StB test points KrG			0412220000				0340620000	0357620000	0324120000 1404620000		
With 2 StB test points KrS									0324130000		
Dimensions											
Width / Length / Height mm (in.) for TS 32			6.5/42/40.5 (.26/1.81/1.60)		6.5/42/57 (.26/1.81/2.24)		6.5/40/67 (.26/1.57/2.64)		12/65/70.5 (.47/2.56/2.76)		
for TS 35			6.5/46/38 (.26/1.81/ 1.50)		6.5/46/54.5 (.26/1.81/2.14)		6.5/49.5/59.5 (.26/1.95/2.34)		12/65/66 (.47/2.56/2.6)		
Insulation stripping length mm (in.)			8 (.31)		8 (.31)		12 (.47)		12 (.47)		
Technical Data											
Rated voltage / rated current / wire size			UL	300 V / 10 A / #22...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 25 A / #22...12 AWG	600 V / 25 A / #22...8 AWG	600 V / 25 A / #22...10 AWG		
			CSA	300 V / 10 A / #26...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 10 A / #22...12 AWG	300 V / 25 A / #22...10 AWG	600 V / 25 A / #20...10 AWG	500 VAC / 27 A / 10 mm²		
			VDE	380 VAC / 10 A / 4 mm²	380 VAC / 10 A / 4 mm²	380 VAC / 10 A / 4 mm²	380 VAC / 25 A / 4 mm²	500 VAC / 27 A / 10 mm²	3.0 (26.0)		
Torque Nm (lb. in.)				0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (8.0 / 4.5 StB)	0.6 / 0.5 StB (7.0 / 4.5 StB)	3.0 (26.0)	4		
Clamping screw			M	3	3	3	3	4			
Selected Accessory Data*											
End Plate (thickness mm)			Type	Part No.	Type	Part No.	Type	Part No.	Type	Part No.	
Beige PA			AP (1.5)	0211360000	AP (1.5)	0211360000					
Blue PA			AP (1.5)	0211380000							
KrG			AP (1.5)	0211320000			AP (1.5)	0117920000	AP (3.0)	0146720000	
KrS									AP (3.0)	0146730000	
Partition (thickness mm)											
PA							TW (1.5)	0130160000	TW (1.5)	0242960000	
KrG									TW (3.0)	0242920000	
KrS									TW (3.0)	0242930000	
HP			TW (1.0)	0297100000	TW (1.0)	0297100000	TW (1.0)	0297100000			
Jumpers											
Final number indicates number of poles. See the Accessories Section for more information. When using QB, maximum conductor connection is 2.5 mm².			QB 2	0482700000	QB 2	0482700000	QB 2	0482700000	QL 2	0135500000	
			QB 3	0482800000	QB 3	0482800000	QB 3	0482800000	QL 3	0135600000	
			QB 4	0482900000	QB 4	0482900000	QB 4	0482900000	QL 4	0135700000	
			QB 25 bare*	0134000000	QB 25 bare*	0134000000	QB 25 bare*	0134000000	QL 10	0338500000	
									VH 14	0299700000	
									BS M 4 x 20	0362800000	
									SS M 4	0136400000	
Plugs											
BST 4							BST 4 red	1339060000			
BST 4			WTR/SAKR	9525900000							
Dummy plug			Test plug	PS 2.3	0180400000	PS 2.3	0180400000	PS 2.3	0180400000	PS 4	0299600000
			Socket							StB 13.5	0135200000
			Diode plug without diode		DLS 2	0321060000					
			Diode plug with diode 1N4007		DLS 2	0630160000					
			Disconnector plug (spare)				TST	1380600000	TST	0462700000	
Extraction Tool											
							0623060000				
Marking Tags			Print								
Note: Part numbers are shown for a single card of pre-printed tags numbered 1-50.			Consecutive horizontal	DEK 5/6.5	0468160001	DEK 5/6.5	0468160001	DEK 5/6.5	0468160001	DEK 5/6	0468660001
			Consecutive vertical	DEK 5/6.5	0468260001	DEK 5/6.5	0468260001	DEK 5/6.5	0468260001	DEK 5/6	0468760001