

Membrane Switch Frontpanel Short Stroke 18 mm



Weblinks

[html-datasheet](#), [General Product Information](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [e-Shop](#), [CAD-Drawings](#), [Product News](#), [Detailed request for product](#)

All Variants

Description	Order Number
MCS 18 IP65 QUADR.	1241.1100



Availability for all products can be searched real-time:<http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

DATA MCS 18		SWITCHES – MOMENTARY ACTION	
		BENEFITS	
		■ Unique mechanical switches with tactile feedback ■ Extremely high life time of 5 million switching ■ Small mounting depth ■ Various lettering options ■ Front and rear tested to degree of protection IP 65	
		MCS 18 gold contacts	MCS 18 silver contacts
Electrical data			
Contact material		gold	silver
Switching voltage	[mV] [V]	min. 50 DC max. 24 DC	min. 5V DC max. 48 DC
Switching current max.	[mA]	80	125
Rated breaking capacity	[W]	0.36	0.72
Lifetime (at rated breaking capacity)		> 10 ⁶	> 10 ⁶
Initial contact resistance, new	[mΩ]	< 50	< 50
Initial contact resistance, after lifetime	[mΩ]	< 150	< 150
Insulation resistance	[Ω]	> 10 ⁸	> 10 ⁸
Contact bounce time	[ms]	typ. 0.1	typ. 0.1
ESD resistance	[kV]	± 16	± 16
Mechanical data			
Actuating force	[N]	3 ± 1	3 ± 1
Contact travel	[mm]	0.5 ± 0.1	0.5 ± 0.1
End stop strength	[N]	> 50	> 50
Lifetime	[operations]	> 1 Mio.	> 1 Mio.
Other data			
Solderability	[°C/s]	235 / 2	235 / 2
Soldering heat resistance	[°C/s]	260 / 5	260 / 5
Ambient temperature	[°C]	-25 – +60	-25 – +60
Storage temperature	[°C]	-25 – +60	-25 – +60
Degree of protection		IP 65	IP 65
Recommended torque	[N/cm]	8	8
Materials			
Socket/ Housing (SSM 27)		Thermoplast PES	Thermoplast PES
Face foil		PETP	PETP
Bezel		Thermoplast PBTP	Thermoplast PBTP
Contact material gold / silver		CuZn 37, 3µm Ni 2µm Au	CuZn 37, 2.5µm Ag
Soldering aid		tinned	tinned

DIMENSIONS MCS 18


SWITCHES—MOMENTARY ACTION

CONSTRUCTION




MCS 18


DIMENSIONS



DRILLING DIAGRAM



CIRCUIT DIAGRAM



OVERVIEW MCS 18

SWITCHES—MOMENTARY ACTION



MCS 18



MCS 18

FEATURES

Contact material	Ag	Au
Degree of protection	IP 65	IP 65

PART NUMBER *

square	1241.1100.	x xxx	1241.1102.	x xxx
round	1241.1104.	x xxx	1241.1106.	x xxx
square with soldering aid	1241.1112.	x xxx		
round with soldering aid	1241.1113.	x xxx		
Colour of bezel				
red	3		3	
grey	6		6	
black	7		7	
alu natural				
Colour of face foil				
red				
green				
Colour of face foil without legend				
yellow		091		091
red		093		093
green		095		095
grey		096		096
black		097		097
white		098		098
Standard lettering				
Order index	see page 29		see page 29	
Accessories				
IP 65 to the front	0098.9201		0098.9201	

* X in the Part No. must be replaced by the desired version




LETTERING

Depending on the application and font, there are various lettering possibilities. The following standards can be used for key letterings:

ORDER INDEX LETTERING

A = 001	P = 016	4 = 031	↕ = 046	EIN = 061
B = 002	Q = 017	5 = 032	→ = 047	AUS = 062
C = 003	R = 018	6 = 033	← = 048	AUF = 063
D = 004	S = 019	7 = 034	↓ = 049	AB = 064
E = 005	T = 020	8 = 035	↑ = 050	ON = 065
F = 006	U = 021	9 = 036	% = 051	OFF = 066
G = 007	V = 022	+ = 037	√ = 052	UP = 067
H = 008	W = 023	- = 038	CTRL = 053	DOWN = 068
I = 009	X = 024	· = 039	RETURN = 054	HIGH = 069
J = 010	Y = 025	x = 040	SHIFT = 055	LOW = 070
K = 011	Z = 026	÷ = 041	LOCK = 056	ON/OFF = 071
L = 012	0 = 027	* = 042	STOP = 057	START = 072
M = 013	1 = 028	= = 043	ENTER = 058	
N = 014	2 = 029	# = 044	BACK = 059	
O = 015	3 = 030	↔ = 045	LINE = 060	



MCS 18, LETTER HEIGHTS AND FONTS

- Single characters, Univers 65
- Legends max. 6 characters in line, Univers 65
- Insert label and front foil anthracite, RAL 7016
- Characters and symbols light grey, RAL 7035