





1. CONNECTORS COMPLY WITH AMP SPEC 108-40012.
2. CONNECTOR DESIGNED FOR 28 AND 26 AWG STRANDED AND SOLID CONDUCTOR RIBBON CABLE ON .050 ϕ .
3. DIMENSION APPLIES TO TERMINATED CONNECTOR.
4. MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC; COLOR: BLACK.
5. STEEL PER QQ-S-698.
6. PH BRZ PER QQ-B-750.
7. GOLD PLATING PER MIL-G-45204, BRIGHT TIN PLATING PER MIL-T-10727, NICKEL PLATING PER QQ-N-290.
8. BRIGHT TIN PLATED.
9. .000030 GOLD ON MATING END, .000100 - .000200 BRIGHT TIN LEAD ON TERMINATION END, ALL OVER .000050 NICKEL ON ENTIRE CONTACT.
10. THE MAX SCREW PENETRATION INTO THE CONNECTOR = .312.



DETAIL Z
SCALE 10:1
ROTATED 180° CW



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. TOLERANCES ON : DECIMALS ± .005 ANGLES ± 2°			CONTRACT NO DR 2-10-86 J. PEACHEY CHK 2-10-86 B. WOLFE APPD 2-10-86 S. GOOD APPD 2-11-86 D. HOFFMAN DSGN APPD OTHER APPD		AMP INCORPORATED Harrisburg, Pa. NAME PLUG ASSY, 50 POSN LOW PROFILE HDF, FRONT METAL SHELL, W/PRE-ASSEMBLED COVER, AMP-LATCH		SIZE D SCALE NTS	FSCM NO 00779	DRAWING NO 746790	SHEET 1 OF 1
--	--	--	--	--	--	--	---------------------------	------------------	----------------------	-----------------