






90800--026	26	(36.80)/1.449	(31.75)/1.250	14	YES
90800--024	24	(34.26)/1.349	(29.21)/1.150	15	YES
90800--022	22	(31.72)/1.249	(26.67)/1.050	16	YES
90800--020	20	(29.18)/1.149	(24.13)/.950	18	YES
90800--018	18	(26.64)/1.049	(21.59)/.850	20	YES
90800--016	16	(24.10)/.949	(19.05)/.750	22	YES
90800--014	14	(21.56)/.849	(16.51)/.650	24	YES
90800--012	12	(19.02)/.749	(13.97)/.550	28	YES
90800--010	10	(16.48)/.649	(11.43)/.450	32	YES
90800--008	8	(13.94)/.549	(8.89)/.350	38	YES
90800--006	6	(11.40)/.449	(6.35)/.250	46	YES
90800--004	4	(8.86)/.349	(3.81)/.150	59	YES
PART NO.	NO. OF CKTS	DIMN. A	DIMN. B	QTY PER TUBE	TOOLED

NOTES:

1) MATERIAL: HOUSING-POLYESTER PBT 15% G.F., UL 94 V-0, BLACK.
TERMINAL- CARTRIDGE BRASS (0.28)/.011 REF THICK

2) SEE PRODUCT SPECIFICATION PS-99020-0011.

ADD CKT.1 INDICATOR EC NO: E2007-0083 DRAWING NO: 127 2006/09/11 CHKD: J.DENNEHY 2006/09/11 APPR: J.DENNEHY 2006/09/11	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 10:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION			
			mm	INCH	DRAWN BY PK	DATE 1994/01/28	TITLE RIGHT ANGLE STRAGGERED PICO FLEX HEADER ASSY (1.25)/.050 CENTRES MOLEX INCORPORATED					
			4 PLACES ±---	±---	CHECKED BY J.DENNEHY	DATE						
			3 PLACES ±---	±.004	APPROVED BY J.DENNEHY	DATE						
			2 PLACES ±0.10	±---	MATERIAL NO.		DOCUMENT NO.	SHEET NO.				
			1 PLACE ±---	±---	ANGULAR ±1/2°		SEE CHART		SDA-90800E		1 OF 1	
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A2 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							