




## WIRING LIST

| P1 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | SHELL      |
|----|---|---|---|---|---|---|---|---|---|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|----|------------|
|    |   |   |   |   |   |   |   |   |   |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    |    | DRAIN WIRE |
| P2 | 1 | 2 | 3 | 4 | 5 | 6 | 7 | 8 | 9 | 10 | 11 | 12 | 13 | 14 | 15 | 16 | 17 | 18 | 19 | 20 | 21 | 22 | 23 | 24 | 25 | SHELL      |

## REMARK:

- 1.CABLE: NON-UL 25C×28AWG(7/0.12 T.C) INSULATION:PVC+DRAIN WIRE (26AWG 7/0.16)+AL/MYLAY+JACKET:PVC COLOR:BEIGE(A-K0) OD =7.0±0.2mm.
- 2.CONNECTOR: P1: DB 25P MALE PIN:GOLD FLASH SHELL:NICKEL PLATED.  
P2: DB 25P FEMALE PIN:GOLD FLASH SHELL:NICKEL PLATED.
- 3.HOOD: P1 & P2 45P PVC MOLDING COLOR:BEIGE(A-K0) .
- 4.ELECTRICAL TEST: 100% OPEN SHORT MISSWIRE TEST.
- 5.PACKING:EACH PCS/POLYBAG.