







REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ECR-16-013298	02JUN2017	FL	SY



- NOTES:

- △ MATERIAL CONTACTS ; PHOSPHORBRONZE
MATERIAL SHIELDING ; PHOSPHORBRONZE
MATERIAL HOUSING ; GLASSFILLED POLYESTER (GRAY)
UL-RATING 94V0.
- △ GENERAL PLATING SPECIFICATION: UNDERPLATING
(ENTIRE CONTACT): 1,27µm NICKEL MIN. AND ACTION
PIN: 0,5µm TIN MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE
SPECIFICATION REFERENCE FOR EACH DASH NUMBER.
- △ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- △ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA GR-1217-CORE
QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- △ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE APPROVED LUBRICANT.
- △ PLATING SHIELD :
CONTACT AREA : 0,76µm Au MIN.
ACTION PIN : 0,5µm Sn MIN.
REMAINDER : Ni
- △ ASSEMBLY PRINTED WITH P/N AND DATE CODE
THE MARKING CAN APPEAR ON THE FRONT SIDE
OR BACK SIDE
- △ HOLE PATTERN FOR FEMALE CONNECTOR TYPE M
55 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- △ ROW "f" 6 PLATED THROUGH HOLES FOR UPERSHIELD
- △ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
- △ AREA RESERVED FOR KEYING PART (BASIC P.N. 100526)
- △ CONTACT CAVITIES (3x) SUITABLE FOR 4,8 DIA. HIGH CURRENT,
HIGH FREQUENCY OR FIBRE OPTIC CONTACTS AS PER DIN 41626
(SEE ALSO NOTE 13).
- △ 1,3 DIA. PLATED-THROUGH HOLES (15x) CAN BE OMITTED
IF SPECIAL CONTACTS WITH CABLE CONNECTION OR FIBRE
OPTIC CONTACTS ARE USED.
- △ THIS ROW OF 11 CAVITIES (B1 TO B11) FOR
CONNECTOR ASSEMBLY PURPOSE ONLY.
- △ NOT PLATED-THROUGH HOLES (3x).
- 16 FITS WITH LOWERSHIELD BASIC P/N 5352112



OBSOLETE			5352177-9
			5352177-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.N.KIRAN	20AUG2004	 TE Connectivity	
		CHK B.MOOIJ	27OCT2004		
DIMENSIONS: mm		APVD B.MOOIJ	27OCT2004	NAME	
TOLERANCES UNLESS OTHERWISE SPECIFIED:  ±0.2		PRODUCT SPEC 108-19082	Z-PACK 2mm HM TYPE M (55 POS.)		
		APPLICATION SPEC 114-19029	PRE-SHIELDED RECEPTACLE		
		WEIGHT 0.000000	SIZE A2	CAGE CODE 00779	DRAWING NO C-5352177
MATERIAL -		FINISH -	RESTRICTED TO -		
		CUSTOMER DRAWING		SCALE 5:1	SHEET 1 of 1
				REV D	