


10	9	8	7	6	5	4	3	2	19203
MATERIAL NO.	ENG. NO.	STUD SIZE	"S" MAX	DESCRIPTION					
192030489	B-S-123-06	6	.149/3.78	LOOSE					
192030043	B-S-123-06T	6	.149/3.78	TAPE					



NOTE(S):

- MATERIAL: STEEL
- WIRE SIZE: 16-14 AWG (1.5-2.5 MM²)
- FINISH: NICKEL PLATING
- PART IS ROHS COMPLIANT.
- AMBIENT OPERATING TEMPERATURE UP TO 900 °F (483 °C).

ADDED OPERATING TEMP EC NO: ETC2007-0297 DRWNEHILE CHKD: JMACNEIL APPR: JMACNEIL	2007/03/13 2007/03/13 2007/03/14	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE IN/MM		SCALE 4:1	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
					mm	INCH	DRAWN BY EHILE	DATE 2006/09/20	TITLE RING TONGUE TERMINAL, 16-14 AWG, KRIMPTITE, 900 DEG F (483 DEG C)			
				4 PLACES	± ---	± ---	CHECKED BY JMACNEIL	DATE 2006/09/20				
				3 PLACES	± ---	± ---	APPROVED BY JMACNEIL	DATE 2006/09/20				
				2 PLACES	± ---	± ---	MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19203-027		SHEET NO. 1 OF 1	
				1 PLACE	± ---	± ---						
ANGULAR ± ---°				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MOLEX MOLEX INCORPORATED						