

DWG. NO. SD-52892-040

F

D

V

C

B

DO NOT SCALE DRAWING

8

7

6

5

4

3

2

1

F

E

D

C

B

A

0

1

2

3

4

5

6

7

8

9

10

11

12

13

14

15

16

17

18

19

20

21

22

23

24

25

26

27

28

29

30

31

32

33

34

35

36

37

38

39

40

41

42

43

44

45

46

47

48

49

50

51

52

53

54

55

56

57

58

59

60

61

62

63

64

65

66

67

68

69

70

71

72

73

74

75

76

77

78

79

80

81

82

83

84

85

86

87

88

89

90

91

92

93

94

95

96

97

98

99

100

101

102

103

104

105

106

107

108

109

110

111

112

113

114

115

116

117

118

119

120

121

122

123

124

125

126

127

128

129

130

131

132

133

134

135

136

137

138

139

140

141

142

143

144

145

146

147

148

149

150

151

152

153

154

155

156

157

158

159

160

161

162

163

164

165

166

167

168

169

170

171

172

173

174

175

176

177

178

179

180

181

182

183

184

185

186

187

188

189

190

191

192

193

194

195

196

197

198

199

200

201

202

203

204

205

206

207

208

209

210

211

212

213

214

215

216

217

218

219

220

221

222

223

224

225

226

227

228

229

230

231

232

233

234

235

236

237

238

239

240

241

242

243

244

245

246

247

248

249

250

251

252

253

254

255

256

257

258

259

260

261

262

263

264

265

266

267

268

269

270

271

272

273

274

275

276

277

278

279

280

281

282

283

284

285

286

287

288

289

290

291

292

293

294

295

296

297

298

299

300

301

302

303

304

305

306

307

308

309

310

311

312

313

314

315

316

317

318

319

320

321

322

323

324

325

326

327

328

329

330

331

332

333

334

335

336

337

338

339

340

341

342

343

344


345

346


EN-02J(097) MXJ-54

Technical drawing of a shaft-hub assembly. The shaft has a diameter of $\text{Ø } 33 \pm 0.02$. The hub has a bore diameter of $(\text{Ø } 80)$. The fit specifications are $E \pm 1$ and 2 ± 0.5 .

1. 製品詳細寸法については図面 SD-52892-040 を参照下さい。
RE DETAILED DIMENSION, SEE SD-52892-040
2. 梱包数量：1000個/リール
NUMBER OF CONNECTORS : 1000PCS/REEL
3. リードテープ長さ LEAD TAPE LENGTH



4. トップテープの剥離強度： 0.1N ～ 1.3N(10 ～ 130gf)
(剥離方向は下図参照)
尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)
PEELING OFF FORCE OF TOP TAPE : 0.1N ～ 1.3N(10 ～ 130gf)
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)
THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED ,DURING TRANSPORTATION.



5. 材料(MATERIAL)
 キャリアテープ(CARRIER TAPE): ポリプロピレン(POLYPROPYLENE)
 トップテープ(TOPTAPE): PET, PE, PEF
 リール(REEL): 紙製(CARD BOARD)
6. 本製品は52892-* * 90の鉛フリー品である。
 THIS PRODUCT IS LEAD FREE OF 52892-* * 90

EC NO. DRWN: CH'K: APPR:		EC NO. DRWN: CH'K: APPR:		EC NO. DRWN: CH'K: APPR:		EC NO. DRWN: CH'K: APPR:		RELEASED EC NO. J2004-1855 DRWN: M.NABEI CH'K: M.SASAO APPR: M.SASAO		DESCRIPTION MATERIAL 材料 FINISH 仕上げ WIRE RANGE 適用電線範圍 REV INS. RANGE 被覆外径		注記参照 SEE NOTES // // //		GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION		DIMENSIONS:		SHT		REV			
																//		☒ mm ☐ INCH				☐ mm ☐ INCH		☒ mm ONLY		REVISE ON CAD ONLY			
																10 UNDER 未滿		±0.2				DRAWN BY & DATE M.NABEI 04/01/09		TITLE: EMBOSSD TAPE PACKAGE FOR 0.5 FPC CONN. ASS'Y ZIF SMT R/A (BTM CONT) E/O TYPE -LEAD FREE- MOLEX INCORPORATED					
																10 OVER 以上		±0.25				CHECKED BY & DATE M.SASAO 04/01/09							
30 OVER 以上		±0.3		APPROVED BY & DATE M.SASAO 04/01/09		CAD FILENAME SD-52892-041.S01		MATERIAL NO. 52892-**95		DRAWING NO. SD-52892-041		SHEET NO. 1 OF 2		SIZE B															
		ANGLE 角度		±3°																									
8		7		6		5		4		3		2		EN-02J(097) MXJ-54															

SD-52892-041.S01

DO NOT SCALE DRAWING

DWG. NO. SD-52892-041

E

D

V



C

B

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	RELEASED EC NO. J2004-1855 DRWN: M.NABEI CHK: M.SASAO APPR: M.SASAO	DESCRIPTION FINISH 仕上げ WIRE RANGE 適用電線範囲 INS. RANGE 被覆外径	MATERIAL 材料 SHEET 1 OF 2 参照 SEE SHEET 1 OF 2
8	7	6	5	4	3	2	1

GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE —//	DESIGN UNITS ☒ mm ☐ INCH	THIRD ANGLE PROJECTION	DIMENSIONS: ☐ mm ☐ INCH ☒ mm ONLY	SHT REV
10 UNDER 未満 10 OVER 以上 30 UNDER 未満 30 OVER 以上	±0.2 ±0.25 ±0.3	DRAWN BY & DATE M.NABEI 04/01/09 CHECKED BY & DATE M.SASAO 04/01/09 APPROVED BY & DATE M.SASAO 04/01/09	CAD FILENAME SD-52892-041.S02	TITLE: EMBOSSD TAPE PACKAGE FOR 0.5 FPC CONN. ASS'Y ZIF SMT R/A (BTM CONT) E/O TYPE -LEAD FREE- MATERIAL NO. 52892-***95	REVISION REVISE ON CAD ONLY
ANGLE 角度 ±3°	MATERIAL NO. 52892-***95			DRAWING NO. SD-52892-041	SHEET NO. 2 OF 2
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.					
SIZE B					



32	33.5	21.6	19.9	16.1	15.9	52892-3095	30
		20.6	18.9	15.1	14.9	-2895	28
		19.6	17.9	14.1	13.9	-2695	26
		18.6	16.9	13.1	12.9	-2495	24
		17.6	15.9	12.1	11.9	-2295	22
24	25.5	16.6	14.9	11.1	10.9	-2095	20
		16.1	14.4	10.6	10.4	-1995	19
		15.6	13.9	10.1	9.9	-1895	18
		15.1	13.4	9.6	9.4	-1795	17
		14.6	12.9	9.1	8.9	-1695	16
		14.1	12.4	8.6	8.4	-1595	15
		13.6	11.9	8.1	7.9	-1495	14
		13.1	11.4	7.6	7.4	-1395	13
		12.6	10.9	7.1	6.9	-1295	12
		12.1	10.4	6.6	6.4	-1195	11
		11.6	9.9	6.1	5.9	52892-1095	10
キャリアテープ幅 CARRIER TAPE WIDTH	E	(D)	(C)	(B)	(A)	MATERIAL NO.	極数 CIRCUIT