



Broadband Solutions
SVADTDCO
Addressable Tap Plug-in Directional Coupler, 10 dB

Electrical Specifications

Insertion Loss at Frequency Band, tap	1.5 dB ±0.5 dB @ 5–1002 MHz
Return Loss at Frequency Band, input, typical	20 dB @ 5–1002 MHz
Return Loss at Frequency Band, tap	20 dB @ 5–1002 MHz

General Specifications

Application	Installation of directional coupler creates a 4-port 11 dB tap or an 8-port 14 dB tap
Brand	HomeConnect®
Package Quantity	20

Packed Dimensions

Height	88.90 mm		3.50 in
Length	63.50 mm		2.50 in
Width	88.90 mm		3.50 in
Shipping Weight	0.09 kg		0.20 lb

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	
ISO 9001:2008	Designed, manufactured and/or distributed under this quality management system