






RECOMMENDED STRIP LENGTH



SUGGESTED
PANEL CUTOUT

RG-174, RG-188 & RG-316	.068	.178	58436-3	227194-3	9-413658-0	329633	1-329632-2	1-329631-2	1-413774-5	413772-3	5413771-3				
RG-58/U, 58A/U, 58B/U,58C/U & BELDEN 88240	.068	.213	58436-1	-	9-221132-0	329633	1-329632-2	1-329631-2	413774-5	413772-1	5413771-1				
FOR USE WITH CABLE	CONTACT CRIMP (HEX)	FERRULE CRIMP (HEX)	DIE SET	TUBING QTY=1	FERRULE QTY=1	GASKET QTY=1	LOCKWASHER QTY=1	JAM NUT QTY=1	CONTACT QTY=1	JACK ASSEMBLY QTY=1	PART NUMBER				
THIS DRAWING IS A CONTROLLED DOCUMENT.							DWN A. FERNANDEZ-DOCK5 22APR2005		 Tyco Electronics Corporation Harrisburg, PA 17105-3608						
							CHK J. HAVENER 22APR2005								
							APVD J. LIPPERT 22APR2005								
							NAME								
							JACK, BULKHEAD, HEX CRIMP, COMMERCIAL BNC								
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .016 4 PLC ± - ANGLES ± -		PRODUCT SPEC - APPLICATION SPEC -		SIZE A1		CAGE CODE 00779		DRAWING NO C=5413771		RESTRICTED TO -	
MATERIAL -		FINISH -		WEIGHT -		CUSTOMER DRAWING		SCALE 4:1		SHEET 1		OF 1		REV A1	