

3-Pin Threaded M8/Pico-Style Splitter Cordset—Flat Junction

Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass (female) and nylon/nickel-plated brass (male) coupling nuts


Conductors: 24 AWG, gold-plated contacts

Voltage/Current Rating: 125V ac/dc, 4.0 A

Temperature: -40° to +105° C

Environmental Rating:

Wiring: Parallel wired Y-cords

Connections				Pinout	Used With
Model	Branches	Trunk	Cable Diameter		
CSB-M831M831	3-Pin Pico QD 2 x 0.20 m Female	0.20 m Male	4.40 mm	Female 	- Connect <i>P4</i> to two lights - Spot Lights - Area Lights - Backlights
Dimensions (mm) 				Male  1 = Brown 3 = Blue 4 = Black	

3-Pin M8/Pico-Style and 4-Pin M12/Euro-Style to Flying Leads Splitter Cordset—Flat Junction



Cable: PVC jacket, PUR (polyurethane) connector body, nickel-plated brass coupling nut

Conductors: 24 AWG (3-pin) or 22 AWG (4-pin), gold-plated contacts

Voltage/Current Rating: 250V ac/300V dc, 4.0 A

Temperature: -40° to +105° C

Environmental Rating: IP67

Connections					
Model	Branches	Trunk	Cable Diameter	Pinout	Used With
CSB-UNT213M831F1241	3-Pin Pico QD 0.3 m Male 4-pin Euro QD 0.3 m Female	Flying Leads 4 m	4.40 mm (branches) 5.50 mm (trunk)	Female  1=Brown 2=White 3=Blue 4=Black Male  1 = NC 3 = Blue 4 = Black	• P4 to High Intensity Area Lights (to strobe from P4)
Dimensions (mm)					
					

4-Pin Snap-on M8/Pico-Style Cordsets

Cable: PVC jacket, PUR (polyurethane) connector body, nylon coupling nut

Conductors: 26 AWG, gold-plated contacts

Voltage/Current Rating: 125V ac/dc, 2.0 A

Temperature: -40° to +90° C

Environmental Rating: IP67

Style	Length	Model	Cable Diameter	Dimensions (mm)	Pinout	Used With
Straight	2.00 m	PKG4-2	3.20 mm		Female 1 = Brown 2 = White 3 = Blue 4 = Black	• QS18 • Q20 • D12 • D10A • S12
Right-Angle	2.00 m	PKW4Z-2	3.20 mm		1 = Brown 2 = White 3 = Blue 4 = Black	