



SCHEMATIC

FEATURES:

- Bantam plugs are molded directly to the cable for optimum durability

MATERIALS:

Bantam Plug: Body – Brass, Insulation – PVC, Color: Black

Audio Cable: Two Conductor Twisted Pair With Spiral Shield, Color: Gray

Capacitance: 40 pF/Ft.

Conductors: 22 AWG, Stranding: 7 x 30

Jacket: PVC, O.D. .180" (4,6mm) Nom., Marking: "POMONA 4279-XX"

Finish: 4279N Brass nickel plated

RATINGS:

Operating Temperature: +50°C (+122°F)

Operating Voltage: 300 VRMS

ORDERING INFORMATION: Model 4279-XX and 4279N-XX

XX = Cable Length, Standard Lengths: 12" (30,5 cm), 24" (61 cm), 36" (91,44cm), 48" (121,92cm), 60" (152,4cm)

Additional lengths can be quoted upon requested.

Ordering Example: 4279-12, Cable length is 12" with non-plated Bantum connector

4279N-24, Cable length is 24 with brass nickel plated Bantum connector

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

Sales: 800-490-2361 Fax: 888-403-3360
Technical Assistance: 800-241-2060

PomonaACCESS 90344 (800) 444-6785 or (425) 446-6010
More drawings available at www.pomonaelectronics.com