

MICRO SWITCH

A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR COMPANY
PRAIRIE, ILLINOIS

FED. MFR. CODE 91929

SWITCH - BASIC

CATALOG LISTING

YZ-2RW84-A2

AYE0500

YZ-2RW84-A2

PAGE 1 OF 1

DRAWING NUMBER

ISSUE 11

REPLACES

RELEASE NO.

CHECK

09JAN06

RJ

CHECK

8 FEB 95

F C093346

DAW

09JAN06


CHECK

21 APRIL 62

DAW

09JAN06

GCH



2X 6-32 UNC X (.219)
BINDING HEAD COMBINATION
TERMINAL SCREW AND
CUPWASHER

NOTE
MOUNTING HOLES WILL ACCEPT PINS OR SCREWS
OF .139 MAX DIA ON 1.000 ± .002 CENTERS

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF MINNEAPOLIS-HONEYWELL REGULATOR CO. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS		ELECTRICAL DATA		SCALE FULL	
OPERATING FORCE----- 1 OZ MAX		CONTACT ARRANGEMENT S P N O		DO NOT SCALE PRINT	
RELEASE FORCE----- 1/8 OZ MIN		BREAK DISTANCE .020 MIN		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±	
DIFFERENTIAL TRAVEL-----.007-.050		-L96- 15A-125, 250, OR 480 VAC 1/2 A-125 VDC; 1/4 A-250 VDC 1/8 HP-125 VAC; 1/4 HP-250 VAC		WEIGHT .073 LB	
OVERTRAVEL-----.219 MIN		-L288- -L306- -L315- CE  05   16A 250V ~ T85 5E4			

MASTER

DRAWN