



CRZ 1362

RoHS COMPLIANT



Har-flex 12P female connector

Har-flex 12P female connector



Part-No. / 产品号码	Length/长度
33 15 243 050 0006 .00	500±5
33 15 243 020 0005 .00	200±3
33 15 243 010 0004 .00	100±3

NOTES/要求:

1.) CABLE MUST BE PERFORMED 100% CONTINUITY TEST AND HI-POT (300VDC) TEST.

2.) CABLE OPERATION TEMPERATURE= -30° C TO +105° C .

3.) WHITE LABEL CONTENT:

DATE CODE & LOT INFORMATION
HARTING P/N & REVISION

01	Add side view.	Lucy.Z	15/04/13
00A	Prototype	Andrew.H	20/10/11
Rev.	Description	Appr.	Date

				All Dimensions in mm Original Size DIN A4		Ref. MB
Free size tol.						Mat.
V=		cm ³ / A=		cm ²		SEE BILL OF MATERIAL
Name		Date		Scale		
Detail				Sheet		
Insp.				1 of 1		
Approved						
Har-Flex female 12pole, double ended						
Flat cable assembly, L=xMM						

HARTING (Zhuhai) Manufacturing Co., Ltd.				HARTING		DWG. TB_33 15 0002 .01	
						No.	