


PRODUCT NO
SEE TABLE

REV	DESCRIPTION	REV'D BY	DATE
E	ECR K40044	WW LEE	07NOV94
F	ECR K50039	WW LEE	07NOV95
G	ECR S60431	JM.COM	05JUL96



CUSTOMER COPY

GEN. TOLERANCES XX $\pm$ 0.3/XX $\pm$.01 XXX $\pm$ 0.13/XXX $\pm$.005 XXXX $\pm$ 0.051/XXXX $\pm$.0020 ANGLES = $\pm 2^\circ$		DO NOT SCALE DWG. 		
DESCRIPTION ECON-STIK HEADER .100/2.54 cc D/R STRAIGHT		NAME BK CHUA		
DATE 05JUL96		DATE 5/3/96		PRODUCT NO. 92849
DRAWN [Signature]		APPROVED [Signature]		
SCALE SHT 1 OF 2				

PRODUCT NO	NO. OF POS.	TOTAL LENGTH	TAIL LENGTH	MATING LENGTH	PLATING TYPE
		DIM. F	DIM. G	DIM. H	
92849-001-XX	2 THRU 72	10,80 / .425	2,41 / .095	5,84 / .230	2u" Au OVER 50u" Ni
92849-002-XX	2 THRU 72	13,03 / .513	2,41 / .095	8,08 / .318	2u" Au OVER 50u" Ni
92849-003-XX	2 THRU 72	11,59 / .456	3,05 / .120	6,00 / .236	2u" Au OVER 50u" Ni


NOTES :

- ① BODY MATERIAL : 20% MIN. GLASS FILLED NYLON.
FLAME RETARDANT PER UL-94V-0.
COLOR : BLACK.
- 2 PIN MATERIAL : BRASS.
- 3 TWO SIDES OF PIN TIPS NOT PLATED. TYPICAL BOTH ENDS.
- ④ 2 LBS / 0,9 KG MIN PIN RETENTION IN EITHER DIRECTION.
- 5 PACKAGE IN POLY BAGS PER BUS-14-099.
- 6 PART NO CONSIST OF;

92849-XXX-XX

NO OF POSITION

BASE P/NO
- 7 FOR EUROPEAN SOURCING , SEE DWG 95266

GEN. TOLERANCES X.X±0.3/X.X±.01 X.XX±0.13/X.XX±.005 X.XXX±0.051/X.XXX±.0020 ANGLES = ±2°		DO NOT SCALE DWG.   			
		NAME	DATE	DESCRIPTION ECON-STIK HEADER .100/2,54 cc D/R STRAIGHT	
DRAWN	BK CHUA	05JUL.96		PRODUCT NO. 92849	
CHECKED		SPTAL		SCALE	
APPROVED		8.7.96		SHT. 2 OF 2	

CUSTOMER COPY