samtec

FLEX STACK

(1,27mm) .050"

DWM, HDWM SERIES



MICRO BOARD STACKER

SPECIFICATIONS

Mates with:
SMS, SLM, RSM

DWM
For complete specifications see www.samtec.com?DWM

Insulator Material:
Top: Black LCP
Bottom: Natural LCP
Terminal Material:
Phosphor Bronze
Plating:
Au or Sn over 50µ" (1,27µm) Ni
Current Rating:
1A
Operating Temp Range:
-55°C to + 105°C with Tin
-55°C to + 125°C with Gold
RoHS Compliant:
Yes

HDWM
For complete specifications see www.samtec.com?HDWM

Same as DWM except not CSA rated.

Processing:
Lead-Free Solderable:
Yes
SMT Lead Coplanarity:
(0,15mm) .006" max

Note: Other Gold plating options available. Contact Samtec.

Note: These Series are non-standard, non-returnable.





TYPE STRIP	– NO. PINS PER ROW	– LEAD STYLE	– PLATING OPTION	– ROW OPTION	– STACKER HEIGHT	– OTHER OPTION
	01 thru 50	Specify LEAD STYLE from chart	–L = 10µ" (0,25µm) Gold contact, Matte Tin on tail –G = 10µ" (0,25µm) Gold on post, Gold flash on tail	–S = Single Row –D = Double Row	–"XXX" = Stacker Height Example: –250 = (6,35mm) .250"	– "XXX" = Polarized Position (Specify position of omitted pin) – SM = Surface Mount (Requires HDWM. 02 thru 40 positions only.) – A = Alignment Pin (Requires HDWM. 6 positions min –D only.) Metal or plastic at Samtec discretion (N/A with –LC) – LC = Locking Clip (Requires HDWM. (5 positions min. –D only) (N/A with –A) (Manual placement required) – P = Pick & Place Pad (Requires HDWM)

DWM
= Standard Board Spacer

HDWM
= High Temp Board Spacer

LEAD STYLE	OAL THROUGH-HOLE	OAL SURFACE MOUNT
–01	(11,43) .450	(8,38) .330
–51	(10,41) .410	—
–52	(10,80) .425	—
–53	(12,83) .505	(9,78) .385
–54	(14,10) .555	(11,05) .435
–55	(15,49) .610	(12,45) .490
–56	(15,88) .625	(12,83) .505
–57	(16,51) .650	(13,46) .530
–58	(17,91) .705	(14,86) .585
–59	(19,18) .755	(15,62) .615
–60	(20,96) .825	—
–61	(26,67) 1.050	—





Due to technical progress, all designs, specifications and components are subject to change without notice.

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC SILICON VALLEY • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683