



This is a sample photo.

ORDER SYMBOL: CAB PC 403018 G

EL.number

EAN: 6418074020208

Sweden:

Denmark: 8212020249

Finland: 3424114

INCLUDING:

Cabinet body, door with EPDM gasket, hinges, latches, mounting screws, and corner plugs.


APPROVALS:

USA: UL Type 1, 4, 4X, 12, 13 (E75645 Vol. 1 Sec. 6); UL 94-V2

EURO: IP 65; UL 94-V2

OTHERS: IEC 529, EEI

FIBOX CAB PC



CAB 40 30 S

TECHNICAL INFORMATION:

Standard colour: RAL 7035

Ingress protection: IP 65 (IEC 529, EN 60529)

Flame resistance: UL 94-V2

Temp.range in cont. use: Max. +80 °C

Temp. range of material: - 40 °C - + 120 °C

ACCESSORIES

Inspection window	L 02	Inspection window	L 24 II
Inspection window	L 04	Ventilation device	MB 10631
Inspection window	L 06		
Inspection window	L 08		
Inspection window	L 10		
Inspection window	L 12		
Inspection window	L 12 II		
Inspection window	L 13		
Inspection window	L 24		