

TECHNICAL SPECIFICATIONS

Materials:

Unshielded Hood: Polyamid - UL-recognised

Operating Temperature: -55°C to +110°C

Thumbscrews: UNC 4-40 (Standard)

Shielded Hood: ABS/PC - UL-recognised


Plating: Nickel over Copper

Operating Temperature: -55°C to +110°C


Thumbscrews: UNC 4-40 (Standard)



MHDAPK 15



MHDAPK 25



Ordering information:

Unshielded Version

Size:	P/N - Kitted:	Product Code:
15-way	6211-0100-32	DAPK15-JS
25-way	6211-0100-33	DAPK25-JS

Ordering information:

Shielded Version

Size:	P/N - Kitted:	Product Code:
15-way	6211-0100-42	DAPK15-JS/MET
25-way	6211-0100-43	DAPK25-JS/MET

Note:

All adapters are delivered with 2 long jackscrews in standard versions as seen in above drawings and ordering information.