







REV.	DATE	DESCRIPTION
A	03/18/05	MODIFY DESCRIPTION - UPDATE DRAWING FORMAT

4.00 [.158] 3.50 [.138]



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:

1. CRIMPED CONTACT PIN
HEX CRIMP SIZE .100"
OR SOLDER.

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.6 - 8mm ± 0.20mm 8 - 30mm ± 0.40mm 30 - 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 - .315 = ± 0.007" .315 - 1.180 = ± 0.015" 1.180 - 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex								
8						DRAWN	G.R.S.	03/18/05										
7	NUT	BRASS	NICKEL	1		CHECKED				PART DESCRIPTION BNC CLAMP PLUG (RG-8/U, 213/U, 214/U CABLE)								
6	WASHER	BRASS	NICKEL	1		ISSUED												
5	GASKET	SILICONE	RED	1		SHEET	1 OF 1			PART NO. 112531								
4	BRAID CLAMP	BRASS	NICKEL	1														
3	CONTACT PIN	PHOS. BRONZE	GOLD	1	CAD FILE C:/112/112531.DWG				DWG. NO.		112531.DWG		REV.	A	SIZE	A	SCALE	NA
2	INSULATOR	TEFLON	NATURAL	1														
1	SHELL/BODY	BRASS	NICKEL	1														
	DESCRIPTION	MATERIAL	FINISH	QTY														