

Product Datasheet Candle Energy Saving Lamps



CANDLE 3W B22	Candle Shaped Lamp 3W (20W) BC (B22)
CANDLE 3W E27	Candle Shaped Lamp 3W (20W) ES (E27)
CANDLE 3W B15	Candle Shaped Lamp 3W (20W) SBS (B15)
CANDLE 3W E14	Candle Shaped Lamp 3W (20W) SES (E14)
CANDLE 5W B22	Candle Shaped Lamp 5W (30W) BC (B22)
CANDLE 5W E27	Candle Shaped Lamp 5W (30W) ES (E27)
CANDLE 5W E14	Candle Shaped Lamp 5W (30W) SES (E14)
CANDLE 7W B22	Candle Shaped Lamp 7W (40W) BC (B22)
CANDLE 7W E27	Candle Shaped Lamp 7W (40W) ES (E27)
CANDLE 7W B15	Candle Shaped Lamp 7W (40W) SBS (B15)
CANDLE 7W E14	Candle Shaped Lamp 7W (40W) SES (E14)
CANDLE 11W B22	Candle Shaped Lamp 11W (60W) BC (B22)
CANDLE 11W E27	Candle Shaped Lamp 11W (60W) ES (E27)

Available as:

- Type: Warm light or Daylight
- Wattage: 3W, 5W, 7W and 11W
- Fitting: BC (B22), SBS (B15), SES (E14) and ES (E27)

Features

- Energy Rating 'A'. Up to 80% energy saving compared to traditional bulbs by using less electricity to reach the equivalent brightness:
 - 3 WATTS = 20 WATTS for a conventional bulb
 - 5 WATTS = 30 WATTS for a conventional bulb
 - 7 WATTS = 40 WATTS for a conventional bulb
 - 11 WATTS = 60 WATTS for a conventional bulb
- Lamp life up to 8000 hours (8 times longer than conventional GLS lamps)
- Not suitable for dimming, electronic switches, photocells, timing devices, dusk to dawn sensors.
- Instant start up
- No flicker and no filament to burn out!
- Switching does not reduce lamp life
- Excellent colour render
- RoHS Compliant