



## Datasheet for part number DEMAMY9P

Our Catalog Part Number: DEMAMY-9P
Our Global Manufacturing Part Number: 051538-0010
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: D*MA

Product Datasheet	
General	D*M High reliable D-Sub Connectors with crimp termination
Wire Gauge Range AWG	Standard: AWG 20-28. High Density: AWG 22-28
Mating Cycles	500
Contact Arrangement	9 contacts size 20
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating	7.5 A max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	steel
Shell Finish	tin
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Crimp
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 2)
Hardware	Dual Float Mount