


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


| BANDING<br>PART NUMBER | COIL BAND WIDTH<br>±.010" [ 0.25 ] | MAT'L<br>TYPE | MAT'L<br>COATING | REQ'D.MLT HEAD<br>PART NUMBER | MAT'L LENGTH     | MAT'L THICKNESS<br>±.001" [ 0.03 ] | MAT'L<br>EDGES |
|------------------------|------------------------------------|---------------|------------------|-------------------------------|------------------|------------------------------------|----------------|
| MBEH-TLR               | .500" [ 12.70 ]                    | 304           | -----            | MTEH-C                        | 250.0' [ 76.2m ] | .010" [ .25 ]                      | NOTE 5         |
| MBEH-TLR316            | .500" [ 12.70 ]                    | 316           | -----            | MTEH-C316                     | 250.0' [ 76.2m ] | .010" [ .25 ]                      | NOTE 5         |
| MBSH-TR                | .625" [ 15.88 ]                    | 304           | -----            | MTHSH-C                       | 200.0' [ 61.0m ] | .015" [ .38 ]                      | NOTE 6         |
| MBSH-TR316             | .625" [ 15.88 ]                    | 316           | -----            | MTHSH-C316                    | 200.0' [ 61.0m ] | .015" [ .38 ]                      | NOTE 6         |
| MBCEH-QR316            | .500" [ 12.70 ]                    | 316           | POLYESTER        | MTHCEH-C316                   | 82.5' [ 25.0m ]  | .010" [ .25 ]                      | NOTE 7         |
| MBCSH-QR316            | .625" [ 15.88 ]                    | 316           | POLYESTER        | MTHCSH-C316                   | 82.5' [ 25.0m ]  | .015" [ .38 ]                      | NOTE 7         |



#### NOTES:

1. INSTALLATION TOOLS:  
RT2HT, ST2MT (MBEH, MBCEH ONLY), PBTMT, RT2HTN
2. BRACKETS [ ] DENOTES DIMENSIONS IN MILLIMETERS
3. SEE TABLE FOR COMPATIBLE BANDING HEAD PART NUMBERS
4. TOLERANCES UNLESS OTHERWISE SPECIFIED:  
.X ± .13 [ 3.30 ]
5. FULLY ROUNDED EDGES
6. BROKEN EDGES TO ELIMINATE SHARP EDGES
7. FULLY COATED MATERIAL:  
COATING THICKNESS: .003"/.007" [ .08/.18 ] PER SIDE

| REV | DATE  | BY   | CHK | APR  | DESCRIPTION                                                                                                                | ECN        |
|-----|-------|------|-----|------|----------------------------------------------------------------------------------------------------------------------------|------------|
| 05A | 4/13  | JAMB | MIM | RGRO | UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO                                                         | SSECN01049 |
| 04A | 7/11  | JAMB | MIM | ---  | NOTE #1 REMOVED INSTALLATION TOOL ST3MT. ADDED INSTALLATION TOOL ST2MT (MBEH, MBCEH ONLY) PBTMT, RT2HTN                    | -----      |
| 03A | 10/08 | JAMB | SKB | ---  | NOTE #1: INSTALLATION TOOL RT1HT REPLACED BY RT2HT                                                                         | -----      |
| 02A | 11/07 | JAMB | EJD | ---  | ©PART NO.MBSH-TR & MBSH-TR316 MAT'L LENGTH CHANGED FROM 200.0' [70.0m] TO 200.0' [61.0m]. ORIG CAD FILE SPEC WAS S41199_02 | -----      |
| 02  | 9/05  | JAMB | EJD | ---  | REMOVED PPTMT, GS4MT, ST2MT & HTMT APPLICATION TOOLS                                                                       | SSECN00049 |
| 01  | 5/05  | JAMB | EJD | JJB  | ⒶREQ'D BANDING HEAD PART NO.MTHCSH-C316 WAS PART NO. MTHCSHD-C316                                                          | 12678      |

| TITLE                                                                                 |      |     |                                                                                       |            |  |
|---------------------------------------------------------------------------------------|------|-----|---------------------------------------------------------------------------------------|------------|--|
| STAINLESS STEEL METAL BANDING CONTINUOUS                                              |      |     |                                                                                       |            |  |
| CUSTOMER DRAWING                                                                      |      |     |                                                                                       |            |  |
| ITEM REVISION NAME                                                                    |      |     |  |            |  |
| N41199BS/05                                                                           |      |     |                                                                                       |            |  |
| DATASET FILE NAME                                                                     |      |     |  |            |  |
| N41199BS_DC/05A                                                                       |      |     |                                                                                       |            |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]                  |      |     | MATERIAL:                                                                             |            |  |
| .x ± .1 [ 2.54 ] .xxx ± .005 [ .127 ]                                                 |      |     | SEE NOTES                                                                             |            |  |
| .xx ± .01 [ .25 ] ANGLES ± 5 °                                                        |      |     | DRAWING NUMBER:                                                                       |            |  |
|  |      |     | N41199BS_DC                                                                           |            |  |
| THIRD ANGLE<br>PROJECTION                                                             |      |     |                                                                                       |            |  |
| DRAWN BY                                                                              | DATE | CHK | SCALE                                                                                 | SHEET      |  |
| JAMB                                                                                  | 5/05 | EJD | NONE                                                                                  | SHT 1 OF 1 |  |
|                                                                                       |      |     |                                                                                       | A          |  |