


NOTES: UNLESS OTHERWISE SPECIFIED

1. P/N: 9202COLOR
HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
FRAME: BRASS. NICKEL PLATED.
CONTACT: BeCu OR PHOSPHOR BRONZE. NICKEL PLATED

2. P/N: 9210COLOR
HOUSING: MOLDED NYLON. AVAILABLE IN TEN COLORS.
END CAP: MACHINED DELRIN. WHITE.
FRAME: BRASS. NICKEL PLATED.

3. P/N: W-200/COLOR
22AWG 65X40 TINNED COPPER
0.070 [1.78] O.D. PVC INSULATION
AVAILABLE IN TEN COLORS.

4. PERFORMANCE
MAXIMUM CURRENT: 2.5 AMPS
MAXIMUM VOLTAGE: 1000 (300 UL) W.V.D.C.
MAXIMUM TEMPERATURE: 221°F (105°C)



		UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: FRACTIONS DECIMALS ANGLES ± .XX ± ± .XXX ±	CONTRACT NO.		E-Z-HOOK DIVISION OF TEKTEST INC. ARCADIA, CA 91006 U.S.A. DESCRIPTION STD BAN PLUG (9202) TO STD BAN SKT (9216) SIZE CODE IDENT NO. DRAWING NO. A 08505 9108 SCALE 1:1 SHEET 1 OF 1
			APPROVALS	DATE	
			DRAWN	R.L. 10/10	
			APPROVED BY		
		MATERIAL SEE NOTE.			
		FINISH SEE NOTE.			
		USED ON			
APPLICATION		DO NOT SCALE DRAWING			