


# Extension Cable

172-0910, 172-0906

**KOBI** CONN

Extension Cable



**DIMENSIONS: mm (in.)**

SPECIFICATIONS	
Molding PVC Color:	Beige
Screw:	4-40
Cable:	28 AWG
Maximum Current:	500mA
Insulator:	PBT with 30% Glass Fiber
Housing:	Nickel Plated Steel
Pin:	Brass Contact 1u" Gold Plated

Mouser Stock No.	Description	L	
		mm	inches
172-0910	DB9P M / 9p F 10 Feet	3050±50	120±.197
172-0906	DB9P M / 9p F 6 Feet	1830±50	72±.197

Date Last Revised: 6/25/12

**Available from Mouser Electronics**  
**1-800-346-6873**  
**[www.mouser.com](http://www.mouser.com)**

KC-300363

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

172-0910, 172-0906

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

172-0910 172-0906