

3M™ Dual Conductor Ground Cord Series 2300

The Dual Conductor Ground Cord Series 2300 is for use with dual conductor wrist straps and 3M™ Workstation Monitors. The Dual Conductor Ground Cord features an improved grip that is wider in diameter and easier to grasp when inserting and removing the cord from the remote unit. Meets the resistance requirements of ANSI/ESD S20.20-2014, EIA 625.



Specifications	
Length	5, 10 or 20 feet
Resistance*	1 megohm
Flex life	≥ 16,000 flexes
Color	Gray
Plug Size	3.4 mm
Plug Type	Straight or Right Angle
Part Numbers	
2360	3M™ Dual Conductor Coiled Cord Series 2360, 5 ft. (1.5 m) practical length
2370	3M™ Dual Conductor Coiled Cord Series 2370, 10 ft. (3.0 m) practical length
2371	3M™ Dual Conductor Coiled Cord Series 2371, 20 ft. (6.1 m) practical length
2360R	3M™ Dual Conductor Coiled Cord, Series 2360R 5 ft. (1.5 m) practical length, with right angle mono plug connection (to be used only with 3M Monitors)
2370R	3M™ Dual Conductor Coiled Cord Series 2370R, 10 ft. (3.0 m) practical length, with right angle mono plug connection (to be used only with 3M Monitors)
2371R	3M™ Dual Conductor Coiled Cord Series 2371R, 20 ft. (6.1 m) practical length, with right angle mono plug connection (to be used only with 3M Monitors)

*Meets the resistance requirements of ANSI/ESD S20.20-2014, EIA 625

3M™ Dual Conductor Ground Cord Series 2300

3M is a trademark of 3M Company.

Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**



Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive
Sanford, NC 27332-9733
Toll-Free: 866-722-3736
International: 919-718-0000
Email: 3mstaticinfo@mmm.com
www.3Mstatic.com

Please recycle. Printed in USA.
© 3M 2014. All rights reserved.
78-9102-1851-6 JHA

Related Products

3M™ Workstation Monitor Model 724

3M™ Wrist Strap Monitor Model 725

3M™ Wrist Strap and Ground Monitor Model 773

3M™ Wrist Strap Monitor Model 790

3M™ Iron Man Plus Workstation Monitor Model CTC331

3M™ Ground Man Plus Ground Monitor Model CTC334

3M™ Dual Conductor Adjustable Fabric Wrist Band Series 2368, Turquoise

3M™ Dual Conductor Adjustable Fabric Wrist Band Series 2368VM (790 only), Gray

3M™ Dual Conductor Metal Wrist Strap Series 2384 (Small)

3M™ Dual Conductor Metal Wrist Strap Series 2385 (Medium)

3M™ Dual Conductor Metal Wrist Strap Series 2386 (Large)

3M™ Dual Conductor Wrist Band Series 4720, Blue