


4

3


2

1

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AF	50		S1	REVISED PER ECO-15-008427	08JUN15	JR	DH



- 1 MATES WITH .032±.001x.250 TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .135 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA

STANDARD		HOUSING:NYLON,COLOR-BLACK TRANSLUCENT RECEPTACLE:BRASS, TIN			9-520183-2		
BULK		HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:BRASS, TIN			5-520183-2		
STANDARD		HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:#3 HARD PH BRONZE, TIN			2-520183-4		
		HOUSING:NYLON,COLOR-RED TRANSLUCENT RECEPTACLE:BRASS, TIN			2-520183-2		
PACKAGING		MATERIAL & FINISH			PART NO		
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 10/18/88		 TE Connectivity			
		CHK JR RUTH 10/18/88					
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME			
		APVD K RANDOLPH 10/21/88		RECEPTACLE ASSY,ULTRA-FAST, .250 SERIES,22-18 AWG -			
		PRODUCT SPEC 108-2043					
		APPLICATION SPEC 114-2123					
		WEIGHT -					
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A3	CAGE CODE 00779	DRAWING NO C-520183	RESTRICTED TO -
		CUSTOMER DRAWING			SCALE 4:1	SHEET 1 OF 1	REV S1