






- 1 MOLDDED PARTS: GLASS-FILLED PBT OR GLASS-FILLED NYLON, UL94V-0 RATED.
COLOR: BLACK
SHELLS: CARBON STEEL.
CONTACTS: PHOS BRONZE.
- 2 SHELLS: 5.08μm [.000200] MIN ZINC WITH YELLOW CHROMATE COATING.
CONTACTS: GOLD FLASH PLATED FOR LENGTH OF 3.81[.150] MIN FROM MATING END,
2.54μm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER
1.27μm [.000050] MIN NICKEL.
3. NOTE DELETED.
4. NOTE DELETED.
5. NOTE DELETED.
- 6 NOTE DELETED.
- 7 SHELLS: 5.08μm [.000200] MIN ZINC WITH YELLOW CHROMATE COATING.
CONTACTS: GOLD PLATED FOR LENGTH OF 3.81[.150] MIN FROM MATING END,
0.76μm [.000030] MIN GOLD IN MATED AREA,
2.54μm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER
1.27μm [.000050] MIN NICKEL.
OR
GOLD FLASH OVER PALLADIUM-NICKEL PLATED FOR LENGTH OF
3.81 [.150] MIN FROM MATING END,
0.76μm [.000030] MIN TOTAL IN MATED AREA,
2.54μm [.000100] MIN TIN-LEAD ON SOLDER END, BOTH OVER
1.27μm [.000050] MIN NICKEL.

OBSOLETE	—	—	205734-9
SUPSD BY 205734-7		4.78 [.188]	205734-8
		4.78 [.188]	205734-7
SUPSD BY 205734-5	—	—	205734-6
		16.54 [.651]	205734-5
		10.85 [.427]	205734-4
SUPSD BY 205734-5		10.85 [.427]	205734-3
SUPSD BY 205734-1		3.18 [.125]	205734-2
		3.18 [.125]	205734-1
	CONTACT FINISH	A	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. POLIGNONE 01FEB07		 TE Connectivity	
		CHK E. BRIANT 01FEB07			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME RECEPTACLE ASSEMBLY, SIZE 1, 9 POSN, VERTICAL, AMPLIMITE HDP —	
		APVD E. BRIANT 01FEB07			
1 PLC ± — 2 PLC ± — 3 PLC ± .005 4 PLC ± — ANGLES ± —		PRODUCT SPEC 108-40025			
MATERIAL		APPLICATION SPEC 114-40013			
FINISH 		WEIGHT —		SIZE A2	CAGE CODE 00779
				DRAWING NO C-205734	RESTRICTED TO —
CUSTOMER DRAWING				SCALE NTS	SHEET 1 of 1
				REV 7	