

# Product data sheet

## Characteristics


# XCSTE7333

## SAFETY INTERLOCK 240VAC 5A T-XCS

Product availability : Stock - Normally stocked in distribution facility



Price\* : 245.00 USD



### Main

Device short name	XCSTE
Enclosure type	Dust and damp proof enclosure indoor/outdoor Corrosion resistance enclosure indoor/outdoor

### Complementary

Line Rated Current	6 A
[Us] rated supply voltage	120 V
Actuator	Key
Contact operation	Slow-break
Contacts type and composition	2 NC
Maximum Depth	1.3 in (33.02 mm)
Electromagnet interlocking	Locking on de-energisation and unlocking on energisation of solenoid
Enclosure material	plastic
Height	3.67 in (93.22 mm)
Locking options description	With locking of actuator, unlocking by key operated lock
Number of poles	2
Permissible voltage	300 V AC

### Environment

Ambient air temperature for operation	-13...140 °F (-25...60 °C)
IP degree of protection	IP67
NEMA degree of protection	NEMA 4/4X/12

### Ordering and shipping details

Category	22411 - LIMIT SWITCHES,IEC,XCKJ
Discount Schedule	T

\* Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

GTIN	00785901825227
Nbr. of units in pkg.	1
Package weight(Lbs)	1.1 lb(US) (0.50 kg)
Returnability	Yes
Country of origin	FR

### Packing Units

Unit Type of Package 1	PCE
Package 1 Height	4.33 in (11 cm)
Package 1 width	1.38 in (3.5 cm)
Package 1 Length	3.74 in (9.5 cm)

### Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Di-isodecyl phthalate (DIDP) and Diisobutyl phthalate (DINP) which is known to the State of California to cause Carcinogen and Reproductive harm. For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) <a href="#">EU RoHS Declaration</a>
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	<a href="#">Product Environmental Profile</a>
Circularity Profile	<a href="#">End of Life Information</a>

### Contractual warranty

Warranty	18 months
----------	-----------