


REV.	DATE	ECR NO.	DESCRIPTION
NC	06/15/98	XXXXXX	INITIAL RELEASE
A	05/13/08	100015	UPDATE DRAWING FORMAT
B	06/21/11	2185	ADD NOTE 1, 2, 3



1. IMPEDANCE: 50 OHMS
2. FREQUENCY RANGE: 0-4 GHz
3. MAX. PANEL THICKNESS: 4.5MM

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex				
DRAWN		M.ZHANG		06/21/11										
6	HEX NUT	BRASS	NICKEL	1		CHECKED	PART DESCRIPTION BNC FEMALE TO FEMALE BULKHEAD ISOLATED ADAPTOR							
5	LOCK WASHER	BRASS	NICKEL	1		ISSUED								
4	INSULATOR	DELFIN	NATURAL	1		SHEET								
3	CONTACT PIN	PHOSPHOR BRONZE	GOLD	1		1 OF 1		PART NO. 112439						
2	INSULATOR	DELFIN	NATURAL	1										
1	BODY	BRASS	NICKEL	1			DWG. NO. 112439.DWG							
DESCRIPTION		MATERIAL	FINISH	QTY	C:/CONNEX/112439.DWG							REV. B	SIZE A	SCALE NA