



- Products
- Distributors
- Knowledge Base
- Downloads
- Calculators
- Technical Help

Knowledge Base

- [Electronic Valve Series Flow Chart](#)
- [Clippard Analytical Series Electronic Valves](#)
- [Clippard Oxygen Clean Electronic Valves](#)
- [Clippard DV Series High Flow Electronic Valves](#)
- [Clippard EMSeries Electronic Valves Press Release](#)
- [Clippard EW Series Electronic Valves Press Release](#)

[more...](#)



ECN-3M-24

Valve Porting

3-Way Normally-Open ▼

Mount

Manifold Mount ▼

Connection Type

0.025" Square Pin Contr ▼

Voltage

24 VDC ▼

Series

Standard ▼

Pressure Range

28" Hg Vac. to 105 psig ▼

Seals

Nitrile ▼

More Views



Product will ship within 5 business days

Qty: 1

Add to Cart

Get CAD files:

Select a format... ▼

Details

2-Way Elec Valve, Norm-Open, Mfld Mnted, 24 VDC

See Catalog: [Page 196](#)

Additional Information

Accessories	2020 2021 EVB-2 EVB-3
Body Material	Nickel Plated Brass
Connection Type	0.025" Square Pin Connector
Connector	AMP #103959-1
Connector P/N	C2-RB18
Flow	0.9 scfm @ 100 psig (25 L/min @ 7 bar)
Life Cycles	Over 1 Billion
Manifolds	Manifolds
Medium	Clean, Dry Air (40 micron filter)
Mount	Manifold Mount
Poppet Travel	0.007"
Power Consumption	0.67 Watts
Pressure Range	28" Hg Vac. to 105 psig
Response Time	5 to 10 milliseconds (nominal) @ 25 psig
Seals	Nitrile
Series	Standard
Valve Porting	3-Way Normally-Open
Voltage	24 VDC



Company History
Our Credo
Community
ISO 9001:2008
Warranty
Privacy Notice
Terms of Use
Careers

Products

[Catalog Home](#)
[Search the Catalog](#)
[Request Literature](#)
[Monthly E-Newsletter](#)

Distributors

[Find a Distributor](#)
[Technical Help](#)
[Trade Show Schedule](#)

Application Ideas

[Product How to's](#)
[Product Tips](#)
[Installation Instructions](#)
[Applications](#)

Downloads

[Full Line Catalog](#)
[Product Brochures](#)
[Training PDFs](#)
[Product Data Bulletins](#)

Toll Free 877.245.6247