




Part Number	Count	A Span	B Span
193-2801-009	9	.450" Nom	.400 ±0.011"
193-2801-010	10	.500" Nom	.450 ±0.011"
193-2801-014	14	.700" Nom	.650 ±0.011"
193-2801-015	15	.750" Nom	.700 ±0.011"
193-2801-016	16	.800" Nom	.750 ±0.015"
193-2801-020	20	1.000" Nom	.950 ±0.015"
193-2801-024	24	1.200" Nom	1.150 ±0.015"
193-2801-025	25	1.250" Nom	1.200 ±0.015"
193-2801-026	26	1.300" Nom	1.250 ±0.015"
193-2801-034	34	1.700" Nom	1.650 ±0.015"
193-2801-036	36	1.800" Nom	1.750 ±0.020"
193-2801-037	37	1.850" Nom	1.800 ±0.020"
193-2801-040	40	2.000" Nom	1.950 ±0.020"
193-2801-050	50	2.500" Nom	2.450 ±0.020"
193-2801-060	60	3.000" Nom	2.950 ±0.020"
193-2801-064	64	3.200" Nom	3.150 ±0.025"

PHYSICAL

CONDUCTORS: 28-7/36 T Cu

INSULATION: .010" TPE

TEMP. RATING: -65° to 125° C

COLOR: TAN

ELECTRICAL

IMPEDANCE: 115 ohms

CAPACITANCE: 11 pF

INDUCTANCE: .18 micro Henries

PROP DELAY: 1.35 ns/ft

CURRENT: 1.3A @ 10° C RISE
ABOVE AMBIENT

DC RES.: 65 ohms
PER 1000 ft MAX

INSULATION RES.: 10¹⁰ ohms - 10 ft MIN.

APPROVALS: UL AWM STYLE 20559
CSA AWM FT-1

Above values measured in the
Ground-Signal-Ground mode

DRAWN	PROD ENG	QA	MKT	ECN#	DRAWING NO. 193-2801-0XX	Amphenol SPECTRA-STRIP Operations 720 Sherman Ave Tel (203) 281-3200 Hamden CT. 06514 Fax (203) 281-5872	Rev A
FITS 11/13/97					TITLE: Spectra-Zip TPE Planar Cable		Sheet
							1 of 1