

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

19324-0005

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp™ Metric Ring Terminal for Stud Size 10 (M5), Insulated Barrel



Series
image - Reference only

Documents:

3D Model

RoHS Certificate of Compliance (PDF)

Drawing (PDF)

Agency Certification

UL

E32244

General

Product Family

Series

Crimp Quality Equipment

Mil-Spec

Overview

Product Name

Type

UPC

Ring and Spade Terminals

19324

Yes

N/A

Metric Ring Terminals

Avikrimp™

Ring

887191290058

Physical

Barrel Type

Flammability

Insulation

Material - Metal

Material - Plating Mating

Net Weight

Packaging Type

Stud Size

Wire Size AWG

Wire Size mm²

Closed - Brazed

94V-2

Nylon (PA)

Copper Alloy

Tin

1.204/g

Bag

10 (M5)

N/A

1 (0.5 – 1)

Material Info

Old Part Number

AA1-822-M5

Reference - Drawing Numbers

Sales Drawing

SD-19324-001

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

19324Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[19324-0005](#)