

181-00249

Solid Wall Wiring Duct, 2" X 5", Non-Adhesive, PVC, White, 30ft/Carton

Article Number: 181-00249

Part Number: 181-00249

Type: SD2X5

[Find a Distributor](#)

[Order Samples](#)

[Get Technical Drawings](#)

[!\[\]\(3342c215b2a8b663596a81468d5dc314_img.jpg\)](#) [!\[\]\(5e22d44aef1f9548ca8274cbfb388e9d_img.jpg\)](#) [!\[\]\(b011182daf5a0527ed818f91dc4cf8f7_img.jpg\)](#) [!\[\]\(e021942709a217cfed2f781c62feb09c_img.jpg\)](#) | [!\[\]\(189fbc627457efb1015bb006253636f9_img.jpg\) Share](#)

[Base Data](#)

Part No.	181-00249
Type	SD2X5
Color	White (WH)
Features	• A temporary film is applied to the covers to protect against scratches and is writable for identification during installation. • Cover is flush with the side of the duct for increased wire capacity and allows for tight, side by side duct placement. • Covers are provided with a non-slip lining, which insures the covers remain in place during vibration, yet they easily snap on and off. (Covers to be purchased separately)

[Product Dimensions](#)

Length (L)	6.0ft / 1.83m
Width (W) (imperial)	2.0"
Width (W)	50.8mm
Width (W2)	2.0" / 50.8mm
Height (H)	5.0" / 127.0mm
Mounting Hole Centers	4.00" / 101.60mm

[Material and Specifications](#)

Material	Polyvinylchloride (PVC)
Flammability	self-extinguishing
Material Specification	RoHS
Operating Temperature	+122 °F (+50 °C)
Specification	UL / CSA
UL Recognized (US and Canada)	Yes

[Logistic and Packaging](#)

Pkg. Qty. 30

[Find a Distributor](#)

[Get Product Samples](#)

[Get Technical Drawings](#)

