

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19

© COPYRIGHT 19

BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
AJ	16				C	OBS -1,-6 & -8 PER 0E10-0116-99	07FEB00	M0





FIG 1




FIG 3




FIG 2

RECOMMENDED STRIP LENGTHS

1. USE HAND TOOL: PRO-CRIMPER #58434-1

	58436-1	FIG 3	RG-58/U & BELDEN YR20621	CONTACT=.068;BRAID=.213	221132-3	414164-4	227112-6	414160-9
OBSOLETE	58436-1	FIG 3	RG-59/U & 62/U	CONTACT=.068;BRAID=.255	2-221132-0	414164-6	227112-5	414160-8
	58436-1	FIG 3	RG-55/U,142/U & 223/U	CONTACT=.068;BRAID=.213	2-221132-6	414164-4	227112-6	414160-7
OBSOLETE	58485-1	FIG 2	RG-216/U	CONTACT=.068;BRAID=.429	2-221132-9	414164-2	227112-1	414160-6
	58485-2	FIG 2	RG-393/U	CONTACT=.128;BRAID=.429	2-221132-9	414163-2	227112-3	414160-5
	58485-2	FIG 1	BELDEN 8214	CONTACT=.128;BRAID=.429	2-221132-3	414163-4	227112-3	414160-4
	58485-1	FIG 2	BELDEN 9880	CONTACT=.100;BRAID=.429	2-221132-9	414116-4	227112-1	414160-3
	58485-1	FIG 2	RG-9/U & 214/U	CONTACT=.100;BRAID=.429	2-221132-9	414116-4	227112-1	414160-2
OBSOLETE	58485-1	FIG 1	RG-8/U & 213/U	CONTACT=.100;BRAID=.429	2-221132-3	414116-4	227112-1	414160-1
DIE SET		STRIP LENGTH	FOR USE WITH:	HEX CRIMP HEIGHTS IN INCHES	③ FERRULE QTY=1	② CONTACT QTY=1	① PLUG ASSY QTY=1	PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± 0.41 [.016] ANGLES ± - MATERIAL - FINISH -				DR M. SNEED 3-22-91		CHK 8-6-91 R. HENRY		AMP Incorporated Harrisburg, PA 17105-3608	
APPD 8-6-91 R. HENRY				APPD 8-6-91 M. SNEED		PRODUCT SPEC -		NAME PLUG, HEX CRIMP, COMMERCIAL, SERIES N	
APPLICATION SPEC -				WEIGHT -		SIZE CAGE CODE 00779		DRAWING NO 414160	
						SCALE 4:1		SHEET 1 OF 1	