

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200795107](#)
Status: **Active**
Overview: [Brad Ultra-Lock Connection System](#)
Description: Ultra-Lock (M12) Single-Ended Cordset, 3 Poles, Male (90°) to Pigtail, 22 AWG, PVC Cable, 2.0m (6.56') Length

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR6837

General
Product Family Industrial Cordsets
Series [120079](#)
Connector End A Ultra-Lock (M12)
Connector End B Pigtail
IP Rating IP69K
Material - Contact Copper Alloy
Overview [Brad Ultra-Lock Connection System](#)
Product Name Ultra-Lock (M12)
Protocol EtherNet
Region Europe
Type Single Ended
UPC 884982224834

Physical
Cable Diameter 5.33mm (.210")
Cable Length 2.0m (6.56')
Color - Cable Jacket Black
Coupling Style Push to Lock
Gender Male-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body TPE
Material - Coupling Nut Nickel-plated Brass
Material - O-Ring Fluoro-elastomer
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 3
Temperature Range - Operating -30°C TO +80°C
Wire Size AWG 22
Wire/Cable Type UL 2464

Electrical
Current - Maximum per Contact 4.0A
Voltage - Maximum 250V AC/DC

Material Info
Engineering Number W03007E03M020

Reference - Drawing Numbers
Sales Drawing 1200795111-000



Series image - Reference only

EU ELV
Not Reviewed

EU RoHS	China RoHS
Not Reviewed	
REACH SVHC	
Not Reviewed	
Halogen-Free	
Status	
Not Reviewed	

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series
[120079](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION