

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300610119](#)
Status: **Active**
Overview: [BradPower Cordsets and Receptacles](#)
Description: BradPower A-Size (7/8"–M22) Single-Ended Cordset, 4 Poles, Female (90°) to Straight, 14 AWG, PVC Cable, 2.0m (6.56') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E258922

General

Product Family Industrial Cordsets
Series [130061](#)
Connector End A BradPower A-Size (7/8"–M22)
Connector End B Pigtail
IP Rating IP67
Material - Contact Copper Alloy
Overview [BradPower Cordsets and Receptacles](#)
Product Name BradPower A-Size
Protocol FF
Region Europe
Type Single Ended
UPC 78678883192

Physical

Cable Diameter 14.99mm (.590")
Cable Length 2.0m (6.56')
Color - Cable Jacket Gray
Coupling Style Threaded
Gender Female-Pigtail
Keyway Single
LED Indicator No
Material - Cable Jacket PVC
Material - Connector Body PVC
Material - Coupling Nut Black Epoxy Coated Zinc
Material - Plating Mating Gold
Orientation 90° to Pigtail
Poles 4
Temperature Range - Operating -20°C to +90°C
Wire Size AWG 14
Wire/Cable Type Unshielded-Stranded

Electrical


Current - Maximum per Contact 15.0A
Voltage - Maximum 600V

Material Info

Engineering Number 104001A46M020

Reference - Drawing Numbers

Sales Drawing SD-130061-014



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China RoHS

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130061](#) Series