





LOC	DIST	REVISIONS					
DF	FO	P	LTR	DESCRIPTION	DATE	DWN	APVD
		G	REV PER	OH14-0207-05	12JAN06	PY	DM



SECTION X-X



- 1 AMP, DATE CODE, & PART NO. MARKED THIS AREA.
- 2 HOUSING MATERIAL: POLYPHENYLENE SULFIDE, GST-40F, PER MIL-M-24519.
- 3 CONTACT MATERIAL: BRASS
- 4 FINISH: .000030 GOLD OVER .000050 NICKEL IN CONTACT AREA.
- 5 FINISH:.000100 TIN LEAD OVER .000050 NICKEL.
- 6 LETTERS INDICATING OUTSIDE ROWS AND NUMBERS INDICATING END CAVITIES MARKED THIS SURFACE.
- 7 NUMBERS INDICATING EVERY FIVE CAVITIES MARKED ON BOTH SIDES.
- 8 LINES INDICATING EVERY FIVE CAVITIES MARKED ON MATING FACE.
- 9 FINISH:.000100 TIN OVER .000050 NICKEL.



9	4.900	49	5.044	5.450	5.750	150	5-531137-4
9	3.400	34	3.544	3.950	4.250	105	5-531137-2
9	2.900	29	3.044	3.450	3.750	90	5-531137-1
8	OBSOLETE	9.900	99	10.044	10.450	300	1-531137-5
8	OBSOLETE	8.900	89	9.044	9.450	270	1-531137-4
8	OBSOLETE	6.400	64	6.544	6.950	195	1-531137-3
8	OBSOLETE	4.400	44	4.544	4.950	135	1-531137-2
8	OBSOLETE	3.200	32	3.344	3.750	99	1-531137-1
8	OBSOLETE	4.100	41	4.244	4.650	126	1-531137-0
8	OBSOLETE	4.000	40	4.144	4.550	123	531137-9
8	OBSOLETE	7.900	79	8.044	8.450	240	531137-8
8	OBSOLETE	6.900	69	7.044	7.450	210	531137-7
8	OBSOLETE	5.900	59	6.044	6.450	180	531137-6
8	OBSOLETE	5.400	54	5.544	5.950	165	531137-5
8	OBSOLETE	4.900	49	5.044	5.450	150	531137-4
8	OBSOLETE	3.900	39	4.044	4.450	120	531137-3
8	OBSOLETE	3.400	34	3.544	3.950	105	531137-2
8	OBSOLETE	2.900	29	3.044	3.450	90	531137-1
E	D	C	B	A	NO. OF POSN.	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN W.D.KISELA 5-10-93	4-6-93	tyco Electronics		Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: INCHES		CHK D.MILLER 5-10-93		NAME		PIN HEADER ASSY, RIGHT ANGLE, 3-ROW, .100	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D.MILLER PRODUCT SPEC		APPLICATION SPEC		RESTRICTED TO	
MATERIAL		FINISH		WEIGHT		A1 00779 ©=531137	
CUSTOMER DRAWING		SCALE 5:1		SHEET 1 OF 1		REV G	