


CONFIGURATION	PART NUMBER	LENGTH
MINI, 4 PIN, 16AWG MALE INLINE STRAIGHT, FEMALE PLUG STRAIGHT	MN47A4AC01Mxxx	AS REQUESTED

DIMENSIONS



TECHNICAL DATA

APPROVALS:	UL, c(UL)
TEMPERATURE RANGE:	-20C to +105C
PROTECTION:	IP 67, NEMA 6P
VOLTAGE RATING:	600VAC
AMPERAGE:	10A
HOUSING:	OIL RESISTANT PVC
CONTACTS:	COPPER ALLOY
CONTACT PLATING:	GOLD OVER NICKEL PLATING
CONNECTOR FACE:	PVC
COUPLING:	MACHINED ALUMINUM, ANODIZED
CABLE CHARACTERISTICS:	STOOV 600V 105°C CSA ST FT2-ROHS PVC INSULATED 16AWG STRANDED COPPER (65x #34)