






## Electrical Specs.


Ind.\* 20nH $\pm$ 5% @ 10MHz.

Q\*\*\* 40 Min. @ 50MHz.

Current Rating\*\* 1.558Adc



Recommended Foot Print



### Notes:

\* Tested on HP 4192A meter

\*\* Rated current is based on a 35°C temperature rise at an ambient temperature of 90°C.

\*\*\* Read on 4342A Q-meter

- Operating temperature -55°C to +125°C

- RoHS Compliant

### Tape and Reel Specs:

Pcs./Reel maximum: 2000  
 Pitch between parts: 8 mm  
 Tape width: 8 mm  
 Reel diameter inches: 7

NEXT ASSEM	USED ON	LTR.	REVISION	BY	DATE

Part #: SM3-020J-1LF

DRAWN BY	KB	APPROVED BY	KB	ENG	QA	MFG
----------	----	-------------	----	-----	----	-----

Unless otherwise specified dimensions are in inches.  
in. (mm)

This drawing or specification is the property of Gowanda Electronics. Copies shall not be reproduced or copied or used as the basis for the manufacture or sale of apparatus without permission.



ONE MAGNETICS PARKWAY  
P.O. BOX 111  
GOWANDA, NEW YORK 14070

Phone Number: (716)532-2234  
Website: [www.gowanda.com](http://www.gowanda.com)