

TN20-6F


BURNDY® PRODUCTS

## TN20-6F

TN20-6F : NYLON FORK 26-20, STUD 4



ACTIVE

[Assistant](#)[Add to Favorites](#)[✉ Email Datasheet](#) [🖨 Print Datasheet](#)

FCI Brings You More

[✉ > Contact our sales/technical support](#)[📄 > Sample request](#)[€ > Price request](#)

## Specifications

[Download document](#)

## Dimensional   Physical   Approvals / Certifications   Other Features

## Dimensional

|                           |           |
|---------------------------|-----------|
| Stud Hole (Size)          | #6<br>#4  |
| Tongue Width (in)         | 0.28 in.  |
| Wire Insulation Grip      | No        |
| Insulation Diameter (Max) | 0.098 in. |

## Physical

|                        |                                      |
|------------------------|--------------------------------------|
| Conductor Size         | 24 AWG<br>20 AWG<br>22 AWG<br>26 AWG |
| Element A Index        | Hand Tools                           |
| Insulation Type        | Nylon                                |
| Color Code             | Amber                                |
| Conductor Size (Range) | 26 AWG to 20 AWG                     |

## Approvals / Certifications

|                 |    |
|-----------------|----|
| Military Listed | No |
| UL Listed       | No |
| CSA Certified   | No |

## Other Features

|                             |              |
|-----------------------------|--------------|
| Tape Mounted Catalog Number | Call Factory |
| Tongue Type                 | Fork         |
| Bulk Catalog Number         | YAE22N66F    |
| UPC                         | 78181073495  |
| Keyword                     | smterm       |