



InstaPATCH® QUATTRO MC Male to MC Male Category 6A U/UTP Bundled Trunk Cable, 4-port, plenum, white

Product Classification

Portfolio	SYSTIMAX®
Brand	InstaPATCH® QUATTRO
Product Type	Copper trunk cable assembly
Regional Availability	Asia Australia/New Zealand EMEA Latin America North America

Dimensions

Cord Length, maximum	90 m 295 ft
Cord Length, minimum	3 m 10 ft

Electrical Specifications

ANSI/TIA Category	6A
dc Resistance, maximum	0.30 ohm
Safety Voltage Rating	1000 V

Environmental Specifications

Environmental Space	Plenum
Flammability Rating	UL 94 V-0
Operating Temperature	-10 °C to +60 °C (+14 °F to +140 °F)
Safety Standard	cETL ETL

General Specifications

Construction Type	Bundled
Interface, connector A	MC Male
Interface, connector B	MC Male
Cable Type	U/UTP (unshielded)
Information Outlet Color	Silver
Interface Feature, connector A	Standard
Interface Feature, connector B	Standard
Jacket Color	White
Package Quantity	1

Pairs, quantity	16
Total Ports, quantity	4

Mechanical Specifications

Conductor Type	Solid
Contact Plating Material	Precious metals
Material Type	Copper alloy Polycarbonate Zinc
Plug Insertion Life, connector A, minimum	100 times
Plug Insertion Life, connector B, minimum	100 times
Plug Retention Force, minimum	133 N 30 lbf
Wiring	T568B

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant
ISO 9001:2015	Designed, manufactured and/or distributed under this quality management system

