

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010112203

Status:


Obsolete

Overview:

kk

Description:

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 20 Circuits



Documents:

Drawing (PDF)

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	7880
Application	Signal
Overview	kk
Product Name	KK®
Physical	
Circuits (maximum)	20
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm (.100")
Stackable	No
Temperature Range - Operating	0°C to +75°C
Material Info	
Old Part Number	7880-20B
Reference - Drawing Numbers	
Product Specification	PS-7879
Sales Drawing	SD-7880

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS

Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

7880Series

Mates With

2.54mm (.100") Pitch KK® Crimp Terminal Housing, High Pressure, 20 Circuits

Use With

7879 KK® High Pressure Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION